

## The next generation of film is here.


After a century of R&D, we're still innovating.

KODAK VISION2 500T Color Negative Film 5218 / 7218 is the start of a new family of films for a new era of filmmaking. An era that demands perfection, but with more efficiency from capture to post. With proprietary new technology for superior image structure; more highlight and shadow detail; improved color and skintone reproduction; clean telecine transfers; and seamless special effects. KODAK VISION2 Film products offer the lowest grain available for clean, crisp images; improved neutral tone scale; and more flexibility in both film and digital postproduction. Yes, it takes film to a whole new level. And after all these years, this is just the beginning.

# KODAK VISION2 500T Color Negative Film 5218 / 7218

www.kodak.com/go/motion





#### BASE

Acetate safety base with rem-jet backing.

#### DARKROOM RECOMMENDATIONS

Do not use a safelight. Handle unprocessed film in total darkness.

## **PROCESSING**

ECN-2

#### STORAGE

Store unexposed film at  $13^{\circ}$ C ( $55^{\circ}$ F) or lower. For storage of unexposed film longer than 6 months, store at  $-18^{\circ}$ C ( $0^{\circ}$ F). Process film promptly.

#### **EXPOSURE INDEX**

Tungsten (3200 K)—500; Daylight—320 (with KODAK WRATTEN Gelatin Filter No. 85)

#### LABORATORY AIM DENSITY

Time negative originals relative to Laboratory Aim Density (LAD) Control Film supplied by Eastman Kodak Company.

#### COLOR BALANCE

This film is balanced for exposure with tungsten illumination (3200 K). You can also expose it with tungsten lamps that have slightly higher or lower color temperatures (± 150 K) without correction filters, since final color balancing can be done in printing. For other light sources, use the correction filters in the table below.

#### POST-PRODUCTION INFORMATION

When you transfer this film directly to video, set up the telecine using negative Telecine Analysis Film (TAF).


LIGHT SOURCE	KODAK FILTERS ON CAMERA*	EXPOSURE INDEX
Tungsten (3000 K)	WRATTEN Gelatin No. 82B	320
Tungsten (3200 K)	None	500
Tungsten Photoflood (3400 K)	None	500
Daylight (5500 K)	WRATTEN Gelatin No. 85	320
White-Flame Arcs	WRATTEN Gelatin No. 85B	200
Yellow-Flame Arcs	Color Compensating 20Y	320
OPTIMA 32	None	500
VITALITE	WRATTEN Gelatin No. 85	320
Fluorescent, Cool White†	WRATTEN Gelatin No. 85 +10M	200
Fluorescent, Deluxe Cool White†	WRATTEN Gelatin No. 85C +10R	320
Metal Halide H.M.I.	WRATTEN Gelatin No. 85	320

\*These are approximate corrections only. Make final corrections during printing.
†These are starting-point recommendations for trial exposures. When you don't know the type of fluorescent lamp, use a KODAK Color Compensating Filter CC40R with an exposure index (EI) of 250.

#### SENSITOMETRIC CURVES ➤


"0" on the x-axis represents normal exposure of an 18-percent gray card in the red, green, and blue layers of this film. A white card is 2 1/3 stops higher than normal exposure, and there are at least 2 1/2 stops above that for capturing specular highlight detail.

A 3-percent black card is 2 2/3 stops below normal exposure. There are at least 2 1/2 stops of latitude below that for capturing shadow detail.




#### MODULATION-TRANSFER CURVES➤

This graph shows a measure of the visual sharpness of this film. The x-axis, "Spatial Frequency," refers to the number of sine waves per millimetre that can be resolved. The y-axis, "Response," corresponds to film sharpness. The longer and flatter the line, the more sine waves per millimetre that can be resolved with a high degree of sharpness—and the sharper the film.




#### DIFFUSE RMS GRANULARITY CURVES ➤

To find the rms granularity value for a given density, find the density on the left vertical scale and follow horizontally to the sensitometric curve and then go vertically (up or down) to the granularity curve. At that point, follow horizontally to the Granularity Sigma D scale on the right. Read the number and multiply by 1000 for the rms value.




#### SPECTRAL-SENSITIVITY CURVES ➤

These curves depict the sensitivity of this film to the spectrum of light. They are useful for determining, modifying, and optimizing exposure for blue- and green-screen special-effects work.



## SPECTRAL DYE-DENSITY CURVES ➤

These curves depict the spectral absorptions of the dyes formed when the film is processed. They are useful for adjusting or optimizing any device that scans or prints the film. NOTE: Cyan, Magenta, and Yellow Dye Curves are peak-normalized.



#### RECIPROCITY

No filter corrections or exposure adjustments for exposure times from 1/1000 of a second to 1/10 second. In the 1-second range, increase exposure 2/3 stop and use a KODAK Color Compensating Filter CC 10R. In the 10-second range, increase exposure 1 stop and use a KODAK Color Compensating Filter CC 10R.

#### **IDENTIFICATION**

After processing, the Kodak internal product code symbol (EH), product code numbers 5218 (35 mm) or 7218 (16 mm), emulsion and roll number identification, and EASTMAN KEYKODE Numbers are visible along the length of the film.

#### GRAIN

The perception of graininess of any film depends on scene content, complexity, color, and density. In KODAK VISION2 500T Color Negative Film 5218 / 7218, the measured granularity is exceptionally low.

#### SHARPNESS

The perceived sharpness of any film depends on various components of the motion picture production system.

Camera and projector lenses, film printers, and other factors play a role, but the specific sharpness of a film can be measured and charted in the Modulation Transfer Curve.

#### Spectral Sensitivity Curve Key

Sensitivity of the yellow dye forming layer
Sensitivity of the magenta dye forming layer
Sensitivity of the cyan dye forming layer

#### Spectral Dye Density Curve Key

Midscale Neutral
 Cyan Dye
 Magenta Dye
 Yellow Dye
 Minimum Density

### KODAK VISION2 500T Color Negative Film 5218 / 7218

#### **ADDITIONAL INFORMATION**

To order the publications below, call 1-800-233-1650 between 8 a.m. and 7 p.m. Eastern Time.

Outside the United States, please contact your Kodak representative.

# Visit us online at www.kodak.com/go/motion

#### **STANDARD PRODUCTS AVAILABLE\***

FORMAT AND SPECIFICATION NO.	LENGTH IN METRES (FEET)	CORE	DESCRIPTION	PERFORATION/PITCH METRIC (IMPERIAL)
35 mm SP718	122 (400)	U		BH-4740 (BH-1866)
35 mm SP718	305 (1000)	U		BH-4740 (BH-1866)
16 mm SP449	30 (100)	R-90 100-ft. spool		2R-7605 (2R-2994)
16 mm SP451	122 (400)	T		2R-7605 (2R-2994)
16 mm SP578	122 (400)	S-153 400-ft. spool		2R-7605 (2R-2994)
16 mm SP426N	15 (50)	R-232 50-ft. spool		2R-7620 (2R-3000)
16 mm SP445**	61 (200)	А	Winding A	1R-7620 (1R-3000)
16 mm SP455	30 (100)	R-90 100-ft. spool	Winding B	1R-7605 (1R-2994)
16 mm SP457	122 (400)	Т	Winding B	1R-7605 (1R-2994)
65 mm SP332	305 (1000)	Р	Emulsion In	KS-4740 (KS-1866)
S8 mm SP464	15 (50)		Super 8 Cartridge	

\*Availability may vary by location.

This product is also available as Finish-to-Order (FTO) in various other standard roll lengths and formats. Sold only in specific minimum order quantities or multiples of the minimum order quantities; non-returnable; US and Canada delivery time of 3 weeks from receipt of purchase order. Other restrictions may apply. Contact your local Kodak representative for additional information.

Burnaby, British Columbia

Orders: 1-800-621-FILM

**EUROPEAN, AFRICAN AND** 

MIDDLE EASTERN REGION

Phone: + 44 1442 846957

29 - 31 Route de L'Aeroport

Phone: +41-22-747-2000

**GREATER ASIA & JAPAN** 

Kodak (Australasia) Pty. Ltd.

Fax: +41-22-747-2200

173 Elizabeth Street

Phone: 61 3 8371 8520

Fax: 61 3 9353 2962

Coburg, Victoria

Australia 3058

Fax: + 44 870 850 2418

Eastman Kodak SA

Le Grand Saconnex

Case Postale 271

1215 Geneva 15

Switzerland

Information:

**REGION** 

**AUSTRALIA** 

Fax: 1-866-211-6311

\*\*Spec 445 can be used only in the AATON A-MINIMA Camera.

For direct ordering in the U.S. and Canada: 1-800-621-FILM (3456)

Suite C150

Canada V5C 6G9

Kodak I imited

**Boundary Way** 

Herts HP2 7YU

Hemel Hempstead

Hemel One

FNGI AND

#### **FILMS**

#### Cinematographer's Field Guide

KODAK Publication No. H-2

#### **PROCESSING**

Manual for Processing KODAK Motion Picture Films, Process ECN-2 Specifications, Module 7

KODAK Publication No. H-24.07

#### **IMAGE STRUCTURE**

#### **KODAK Motion Picture Film**

KODAK Publication No. H-1

#### **TRANSFER**

KODAK Telecine Analysis Film User's Guide

KODAK Publication No. H-822

#### KODAK Telecine Exposure Calibration Film User's Guide

KODAK Publication No. H-807

#### LAD

#### LAD - Laboratory Aim Density

KODAK Publication No. H-61

#### **STORAGE**

#### **KODAK Motion Picture Film**

KODAK Publication No. H-1

(All of the above are also available at http://www.kodak.com/go/motion)

#### The Book of Film Care

KODAK Publication No. H-23

# 

#### Hollywood, California

6700 Santa Monica Boulevard Los Angeles, California

90038-1203

Phone: 323-464-6131 Orders:1-800-621-FILM

#### New York, New York

360 West 31st Street New York, New York 10001-

2727

Phone: 212-631-3400 Orders:1-800-621-FILM

#### **LATIN AMERICA REGION**

Entertainment Imaging 1900 NW 97th Avenue Miami, Florida 33172 Phone: 305-378-0566 305-229-0422

#### CANADA

Kodak Canada Inc. 3500 Eglinton Avenue West Toronto, Ontario Canada M6M 1V3 Phone: 416-761-4922 Orders: 1-800-621-FILM Fax: 416-761-4948

Fax: 416-761-4948 Toll Free Fax: 1-866-211-6311

Kodak Canada Inc. 4 Place du Commerce, Suite 100 Ile des Soeurs Verdun, Quebec Canada H3E 1J4 Orders: 1-800-621-FILM

# Fax: 1-866-211-6311

Express Delivery Service (U.S. only)

1-800-404-2016

(Visa or MasterCard onlyservice fee applies)

# Kodak Canada Inc. CHINA (Peoples Republic) 4185 Still Creek Drive

Beijing: 8610 6561 6561 Shanghai: 8621 6350 0888 Guangzhou: 8620 8666 9888

HONG KONG

Phone: 852 2564 9351

INDIA

Phone: 91 5641 6770

INDONESIA

Phone: 62 21 570 5212

JAPAN

Phone: 813 5540 2280

**KOREA** 

Phone: 822 708 5830

**MALAYSIA** 

Phone: 603 7680 3338

**NEW ZEALAND** 

Phone: 649 302 8665

**PAKISTAN** 

Phone : 92 21 561 0150

**PHILIPPINES** 

Phone: 632 813 7916

SINGAPORE

Phone: 65 6371 3388

**TAIWAN** 

Phone: 8862 2316 8282

**THAILAND** 

Phone: 662 271 3040-59,

Ext. 312

